

REVISION AA

DO NOT SCALE
FROM THIS PRINT






TABLE 2		
LEAD STYLE	NO. OF POS	PACKAGING
-01	-02 THRU -04	TAPE & REEL
-01	-05 THRU -50	PT-1-24-07-15
-02	-02 THRU -05	TAPE & REEL
-02	-06 THRU -50	PT-1-24-07-15
-04	-02 THRU -03	TAPE & REEL
-04	-04 THRU -50	PT-MMT001-DH-P



FTSH-1XX-XX-XX-MT-XX


No OF POS. PER ROW
-02 THRU -50
(SEE NOTE 2 & 5)

LEAD STYLE
-01: "A" = .120 [3.05]
-02: "A" = .075 [1.91]
-04: "A" = .150 [3.81]
(SEE TABLE 1 FOR
TERMINAL USAGE)

PACKAGING
-TR: TAPE AND REEL
DOUBLE MIXED TECHNOLOGY

PLATING

- L: 10μ" LIGHT SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- F: 3μ" FLASH SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- S: 30μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- H: 30μ" HEAVY GOLD IN CONTACT AREA, 3μ" GOLD ON TAIL
- SM: 30μ" HEAVY SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- LM: 10μ" LIGHT SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- FM: 3μ" FLASH SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- TM: MATTE TIN ON CONTACT AND TAIL
- G: 10μ" GOLD IN CONTACT AREA, 3μ" GOLD ON TAIL




DETAIL 'A'

TABLE 1			
LEAD STYLE	"A"	ROW 1	ROW 2
-01	.120±.005 [3.05±.13]	T-1S15-17-XXX	T-1S15-17-XXX
-02	.075±.005 [1.91±.13]	T-1S15-18-XXX	T-1S15-18-XXX
-04	.150±.005 [3.81±.13]	T-1S15-17-XXX	T-1S15-17-XXX


NOTES:

- TERMINALS TO BE SHEARED TO MEET DIMENSION SPECIFICATION.
- PARTS MAY BE CUT TO POSITION.
- MINIMUM PUSHOUT FORCE: .5 LB.
- MAXIMUM TOP / BOTTOM BOW: .004 [.10].
- SEE PACKAGING TABLE 2.
- $\text{\textcircled{C}}$ REPRESENTS A CRITICAL DIMENSION
- .002 MAX BURR ALLOWED.
- .015 MAX CUT FLASH ALLOWED.
- FIRST AND LAST PIN OF ROW 2 TO BE FLUSH TO .003 ABOVE OR BELOW LINE MADE BY BODY.
- MAXIMUM HEIGHT VARIATION BETWEEN ROWS: .005[0.13].


PT-1-24-07-15
(-01, -02 LEAD STYLE)
TUBE TO USE (2) TP-03




PT-MMT001-DH-P
(-04 LEAD STYLE)
TUBE TO USE (2) TP-09




IN-PROCESS 1



IN-PROCESS 2



IN-PROCESS 3



PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, AND OTHER RIGHTS ARE RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE REPRODUCED, COPIED, OR PART OF ANY UNAUTHORIZED PRESENTATION OR INCORPORATED IN ANY OTHER PRODUCT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY:
PURVIS 07-29-96

FTSH-1XX-XX-XX-MT-XX

SHEET 1 OF 1